

Horizontal Cylindrical Pressure Steam Sterilizer-(microcomputer control)

Characteristics:

- Sterilizing course automatic sterilization controlled by computer, easy to operate.
- 2. With drying function, suitable dressing drying.
- 3. With over-temperature, over-pressure auto-protect device.
- 4. The door opening mechanism cannot be operated until the pressure in the chamber is reduced to 0.027 MPa. It can 't be start on if the doesn 't closed well.
- 5. The safety value will be open automatically when the inner pressure over 0.24 MPa, and the steam be exhausting to the water tank.
- 6. The power will be cut-off automatically, cut-off the water and alarm when the machine lacking water.
- 7. The chamber of the sterilizer is made of stainless steel.
- 8. With printer.



| Model | Capacity | Working pressure | Working temperature | Temp. range | Timer | Time of drying | Heat average | Power | Exterior size(cm) | Packing size(cm) | G.W/N.W |
|------------|---------------------|------------------|---------------------|----------------|----------|----------------|--------------|-------------------|-------------------|---------------------|-------------|
| FSF-150YDB | 150L Ф440×1000mm | | 134°C | 40°C-134°C | 0-99 min | 0-99min | ≤±2°C | 9KW/380V 50Hz | 140×65×160 | 156×82×182 | 430kg/340kg |
| FSF-200YDB | 200L Ф515×1000mm | 0.22Mpa | | | | | | 9KW/380V 50Hz | 140×75×170 | 156×91×188 | 436kg/350kg |
| FSF-280YDB | 280L Ф600×1000mm | | | | | | | 12KW/380V 50Hz | 152×91×190 | 168×108×210 | 570kg/462kg |

Table Top Steam Sterilizer

- 1. Sterilizing course automatic sterilization controlled by computer, easy to operate.
- 2. With drying function, suitable dressing drying.
- 3. With over-temperature, over-pressure auto-protect device.
- 4. The door opening mechanism cannot be operated until the pressure in the chamber is reduced to 0.027 MPa. It can 't be start on if the doesn 't closed well.
- 5. The safety value will be open automatically when the inner pressure over 0.24MPa, and the steam be exhausting to the water tank.
- 6. The power will be cut-off automatically, cut-off the water and alarm when the machine lacking water.
- 7. The chamber of the sterilizer is made of stainless steel.

Packing size

G.W/N.W

8. With printer.



700×580×500mm

44kg/40kg



800×580×500mm

50kg/45kg